

M-Series (Magnetic Drive Gear Pumps)

MODELS 2282-M05X02

DESCRIPTION

Flight Works M-Series (Magnetic Drive) Gear Pumps offer the highest level of quality, reliability and versatility in the Flight Works product catalog. The 2282-M05X02 model uses precision-machined parts, magnetic coupling mechanics, and a high-end brushless motor to produce exceptional performance with the highest possible operating life and reliability. The Swiss-made motor allows for varied control options with minimal power draw, while the tight tolerances of both the driving and driven pump components raise performance to optimal levels.



STANDARD SPECIFICATIONS

Diff. Pressure (Max)	 225 psid (fluid dependent; see data charts)
Max Flow Rate	 2500 mL/min
Weight	 265 grams
Fluid Temp.	 -30 to 100 °C (-22 to 212 °F)
Port Size(s)	 See Configuration Options
Std. Voltages	 12 V (X02)
Permissible Fluids	 Alcohols, Water, Light Fuels/Oils, Glycol
(Configuration Specific)	Solutions, Hydraulic Fluids, etc.
Control Options	 Open-Loop Control (Voltage)
(requires controller)	Closed-Loop Control (RPM/Current)

APPLICATIONS

All Flight Works micro gear pumps feature a level of versatility and customization that allows for use in a wide field of applications, including:

- Aerospace
- Instrumentation
- Medical & Laboratory
- Hydraulics
- Cooling
- Food/Beverage/Pharmaceutical
- Fuel Cells

MINPORTANT

This pump is designed to run with an inlet filter (10-50 microns recommended). It may be possible to operate the pump outside of these design limits in certain applications, but this must be checked and validated by the customer.

Specifications and data in this document are for informational purposes only, may vary depending on the system in which the pump is integrated, and are subject to change without notice. Flight Works, Inc. makes no warranties concerning the suitability of this pump for a particular application; as such, it is the customer's responsibility to determine the safety and technical suitability of the system. Refer to the Pump User Guide for more details on handling, setup, operation, and more. This pump is a precision unit, built and assembled as a complete product. Opening, adjusting, or dropping the pump can permanently damage assembly integrity. Please contact Flight Works, Inc. by phone or email with any further questions regarding this product or its function.

Made in the USA

32-M05X0



CONFIGURATION OPTIONS


WETTED MATERIALS			
-O & -H*	-W*	CUSTOM	
 Hard-Anodized Aluminum 52100 Alloy Steel 300- & 400-Series, & 17-4 PH SS 932 Bearing Bronze Viton[®] Samarium Cobalt Loctite[®] 4204 *For use w/ fuels, light oils, and hydraulic fluids 	 Hard-Anodized Aluminum Silicon Carbide 300-Series & 17-4 PH SS 932 Bearing Bronze Viton[®] Samarium Cobalt Loctite[®] 4204 *For use w/ water and mildly corrosive solutions 	 Hastelloy® Titanium PEEK Plastic Acetal PTFE Alumina Zirconia Buna Nitrile EPDM 	

	-O/-W: 6mm Push-to-Connect Fittings (M6 Ports)		
	-H: 1/8" Compression Fittings (NPT Ports)		
INTERFACE	Custom Options: Push-to-Connect, Compression, AN Fittings (5/16-24 Ports w/ O-Ring Boss Seal per AS5202-02), Custom Covers (manifold-mount, alternate port type or orientation, integrated valves etc.)		

Additional custom configurations/materials can be provided upon request (ex. welding, custom wiring, alternate seals, etc.)

DIMENSIONS (mm) & WIRING

-O/-W COVER




-H COVER (adds approx. 10mm to length)

GREY

Hall Sensor 3

0220



Refer to the Pump User Guide and/or Control Instructions manuals for important information on mounting and control setup.

SEE PAGE 3 FOR PERFORMANCE DATA

COMMON ACCESSORIES (Contact Flight Works to Purchase)

FLOW SYSTEM ITEMS

- Filters
- Fittings: Tee/Elbow/Y/Adapters
- Valves: Ball/Check/Needle

- **CONTROL COMPONENTS**
- **Speed Controllers**
- **Pressure Gauges/Regulators** •

TUBING

- Polyurethane Tubing: 3, 4, 6mm
- Tygon Tubing: Medium, Large •
- Stainless Steel Tubing: 1/16", 1/8" •



Water (\approx 1 cP) Heavy Fuel (\approx 2 cP) 3000 3000 17500 17500 2500 **RPM** 2500 RPM 12 V Input 12 V Input Flow Rate (ml/min) 1200 1000 Flow Rate (ml/min) 1200 1000 Voltage Voltage 7500 7500 RPM RPM 500 500 0 0 0 20 40 60 80 100 0 25 50 75 100 125 Pressure (psid) Pressure (psid) **Nominal Voltage Speed Constant Max Continuous Current** X02 12 V 1230 RPM/V 6.40 A

> NOTES: Dashed lines indicate <u>intermittent</u> operation; speed constant may vary at higher pressures; RPM flow lines indicate performance at typical maximum and minimum speeds;

